



Pushing Performance

Han PushPull SCRJ POF Plastic



Image is for illustration purposes only. Please refer to product description.

Part number	09 35 241 0421
Specification	Han PushPull SCRJ POF Plastic
HARTING eCatalogue	https://b2b.harting.com/09352410421

Identification

Category	Connectors
Series	Han® PushPull (V14)
Identification	SCRJ
Element	Connector sets
Specification	PROFINET-Identification: PROFINET O-Plug SCRJ 1 mm POF
Features	Intuitive locking mechanism

Version

Shielding	Unshielded
Number of contacts	2
Locking type	PushPull
Details	When installing a PROFINET system, observe the PROFINET installation guideline.
Pack contents	inkl. housing, SCRJ insert und POF contacts

Technical characteristics

Wire outer diameter	≤2.2 mm
Ferrule diameter	2.5 mm
Limiting temperature	-40 ... +70 °C
Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP65 IP67



Pushing Performance

Technical characteristics

Cable diameter 6.5 ... 9.5 mm

Material properties

Material (hood/housing)	Thermoplastic
Colour (hood/housing)	Black
Material (O-ring)	NBR
Material (cable seal)	TPE
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel
	Lead
	Antimony trioxide

Specifications and approvals

Specifications	IEC 61076-3-117 Variant 14 (V14)
	IEC 61754-24 Mating face
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	27.4 g
Country of origin	Germany
European customs tariff number	85389099



Pushing Performance

Commercial data

eCl@ss	27440101 Rectangular connectors (set)
--------	---------------------------------------