

Part Number : [190740017](#)

Product Description : Krimptite Star Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 8 (M4), Carton

Series Number : 19074

Status : Active

Product Category : Ring and Spade Terminals

Engineering Part Number : SRB-129-08



Documents and Resources

Drawings

[190740017_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)


[Creo](#)

Specifications

[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19074
Description	Krimptite Star Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 8 (M4), Carton
Keyword	Ring Terminal, Ring Terminals
Product Name	Krimptite
Style	Ring
Type	Ring Terminal
UPC	800755072778

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	0.554/g
Packaging Type	Carton
Stud Size	8 (M4)

Termination Interface Style	Crimp or Compression
Wire Size (AWG)	14, 16

Application Tooling

Global

Description	Part Number
Hand Crimp Tool	<u>640031200</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640071200</u>

This document was generated on May 16, 2026