

Detailed Specifications

Frame Width:	60[mm]
Frame Height:	60[mm]
Frame Depth:	20[mm]
Max. Air Flow:	30.37[CFM]
Max. Air Flow:	0.86[m3 per min]
Max. Static Pressure:	0.76[In H2O]
Max. Static Pressure:	109[Pa]
Fan Speed:	6400[RPM]
Noise:	42.5[dB]
Life Expectancy:	40,000 hours at 60C[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	24[V]
Operating Voltage - Lower:	9[V]
Operating Voltage - Upper:	24.6[V]
Current:	0.1[A]
Input Power:	2.4[W]
Mass:	56[g]
Tach / Locked Rotor Output:	No
Status:	Active