

Shrink sleeve - WMS 19,1 (EX30)R YE - 0800306

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Shrink sleeve, Roll, yellow, unlabeled, can be labeled with: THERMOMARK W, THERMOMARK ROLL, THERMOMARK X1.2, THERMOMARK ROLL X1, Unperforated, Mounting type: slide on, Cable diameter: 6.4-19.1 mm, Lettering field: 30 x 20000 mm

Why buy this product

- ✓ Available in the form of continuous rolls and can be printed on both sides using the THERMOMARK W2 printer
- ✓ The shrink sleeves are automatically perforated or cut to the required length during the printing process
- ✓ CSA.C22.2 No. 198.1 (125°C, 600 V, all tubing)
- ✓ MIL-STD-202G, SAE AMS-DTL-23053, SAE AS-81531
- ✓ UL 224 (125°C, 600 V, all tubing)
- ✓ Individual markers can be cut to any length up to 1 m

RoHS

Key Commercial Data

Packing unit	1 STK
Weight per Piece (excluding packing)	550.000 g
Custom tariff number	39173200
Country of origin	China

Technical data

Dimensions

Length (b)	20 m
Width (a)	30 mm
Cable diameter	6.4 mm ... 19.1 mm

Ambient conditions

Ambient temperature (operation)	-55 °C ... 135 °C
---------------------------------	-------------------

General

Color	yellow
-------	--------

Shrink sleeve - WMS 19,1 (EX30)R YE - 0800306

Technical data

General

Base element material	polyolefine
Components	Halogen-free
Material	Polyolefine
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	660
Number of individual labels per row	1
Marking mounting type	slide on

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27400401
eCl@ss 5.1	27400401
eCl@ss 6.0	27400401
eCl@ss 7.0	27400401
eCl@ss 8.0	27400105
eCl@ss 9.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC001530
ETIM 4.0	EC000217
ETIM 5.0	EC000217
ETIM 6.0	EC000217

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504

Shrink sleeve - WMS 19,1 (EX30)R YE - 0800306

Accessories

Accessories

Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110-WMSU - 0801358



Ink ribbon, specifically for WMS... shrink sleeves, length: 300 m, width: 110 mm, color: black

Ink ribbon - THERMOMARK-RIBBON 64-WMSU - 0801360



Ink ribbon, specifically for WMS... shrink sleeves, length: 300 m, width: 64 mm, color: black

Ink ribbon - THERMOMARK-RIBBON 64-WMSU WH - 0801361



Ink ribbon, specifically for WMS... shrink sleeves, length: 300 m, width: 64 mm, color: white

Ink ribbon - THERMOMARK-RIBBON 110-WMSU WH - 0801359



Ink ribbon, specifically for WMS... shrink sleeves, length: 300 m, width: 110 mm, color: white

Printing system accessories

Shrink sleeve - WMS 19,1 (EX30)R YE - 0800306

Accessories

Media hub - THERMOMARK ROLL-ERH - 5146448



External media hub, for the THERMOMARK ROLL, for roll diameter of 150 to 400 mm

Phoenix Contact 2017 © - all rights reserved
<http://www.phoenixcontact.com>