



Part Number : [1301420019](#)

Product Description : Super-Safeway Connector with Locking Blade, 4 Pole/4 Wire, Non-NEMA, 208V, Cord Grip Body Size F4

Series Number : 130142

Status : Active

Product Category : Wiring Devices

Engineering Part Number : 2709

Documents and Resources

Drawings

[1301420019 sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Wiring Devices
Series	130142
Description	Super-Safeway Connector with Locking Blade, 4 Pole/4 Wire, Non-NEMA, 208V, Cord Grip Body Size F4
IP Rating	N/A
NEMA Configuration	Non-NEMA Locking
Product Name	Super-Safeway
Specialty	N/A
Type	Connector
UPC	78678870591

Agency

CSA	LR6837
UL	E10176

Electrical

Current - Maximum per Contact	20.0A
GFCI	No
Voltage - Maximum	208V

Physical

Cord Type	N/A
Flange	No
Flip Lid	No
Gender	Female
Length	N/A
Lighted Connector	No
Locking Blade	Yes
Poles	4-pole/4-wire

Receptacle Type	Single
-----------------	--------

This document was generated on Jan 01, 2026