



**Part Number :** 1301070043  
**Product Description :** Watertite Wet Location  
26W Fluorescent Stringlight 12/3 SOOW 5  
Lamps Lead, 19.81m (65.0') Cord Length  
**Series Number :** 130107  
**Status :** Active  
**Product Category :** Lamps and Lights  
**Engineering Number :** 387510A



---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Lamps and Lights

Series	130107
Description	Watertite Wet Location 26W Fluorescent Stringlight 12/3 SOOW 5 Lamps Lead, 19.81m (65.0') Cord Length
NEMA Configuration	NEMA 5-15
NEMA Rating	NEMA 4X
Product Family	Stringlights
Product Name	Watertite
Type	String Lights
UPC	78678834337

## Electrical

Lamp Wattage - Maximum	26W
Lumens	1800
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

## Physical

Bulb Type	Fluorescent
Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A
Cord Type - Primary	12/3 SOOW
Depth	59.70m (2.350")
Duty	Wet Location
Guard Included	No
Guard Type	Steel
Height	445.01mm (17.520")
Lamp Type	PL-C 26/41/4P
Length	19.81m (65.0')
Material - Globe	Butyrate
Material - Guard	N/A
Mounting Style	Stringer
Outlet	None
Packaging Type	Carton
Socket Construction	Rubber Molded

---

---

This document was generated on Sep 30, 2023