




**Part Number :** [901600150](#)

**Product Description :** 2.54mm Pitch C-Grid III Crimp Housing Dual Row, 50 Circuits, Black

**Series Number :** 90160

**Status :** Active

**Product Category :** Connector Housings



---

## Documents and Resources

### Drawings

[901600150\\_sd.pdf](#)

[PK-90160-0001-001.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)


### Specifications

[PS-99020-0001-001.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |   |
|--------------------|---|
| GADSL/IMDS         | Not Relevant  |
| China RoHS         |  per SJ/T 11365-2006 |
| EU ELV             | Not Relevant  |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21  |
| REACH SVHC         | Contains Triphenyl-phosphate per D(2025)7771-DC (04 Feb 2026)   |
| EU RoHS            | Compliant per EU 2015/863   |

### Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

|              |  |
|--------------|--|
| Status       | Active   |
| Category     | Connector Housings   |
| Series       | 90160  |
| Description  | 2.54mm Pitch C-Grid III Crimp Housing Dual Row, 50 Circuits, Black |
| Application  | Signal, Wire-to-Board  |
| Product Name | C-Grid III   |
| UPC          | 800753534117   |

### Agency

|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

### Physical

|                    |            |
|--------------------|------------|
| Circuits (maximum) | 50         |
| Color - Resin      | Black      |
| Gender             | Receptacle |
| Glow-Wire Capable  | No         |
| Material - Resin   | PPO        |
| Net Weight         | 3.511/g    |
| Number of Rows     | 2          |

|                               |                |
|-------------------------------|----------------|
| Packaging Type                | Bag            |
| Panel Mount                   | No             |
| Pitch - Mating Interface      | 2.54mm         |
| Temperature Range - Operating | -55° to +105°C |

## Mates With / Use With

### Use with Part(s)

| Description   | Part Number      |
|---|------------------|
| Pre-Crimped Lead C-Grid III Female-to-C-Grid III Female, Tin (Sn) Plating, 150.00mm Length, 22 AWG, Black | <u>797582022</u> |
| Pre-Crimped Lead C-Grid III Female-to-C-Grid III Female, Tin (Sn) Plating, 300.00mm Length, 22 AWG, Black | <u>797582023</u> |
| C-Grid III Female Crimp Terminals   | <u>90119</u>     |

---

This document was generated on May 13, 2026