Part Number : 638135700
Product Description : Extractor Tool for CTX64 Female Crimp Terminals
Series Number : 207121
Status : Active
Product Category : Crimp Presses and Crimp Hand Tools



Documents and Resources

Tooling Specifications

ATS-638135700-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	207121
Description	Extractor Tool for CTX64 Female Crimp Terminals
Function	Extraction
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	PremiumGrade
Tool Type	Extraction Hand Tool
UPC	884982012738
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight	226.000/g

Downloaded from Arrow.com.

Applicable Parts

Description	Part Number
Milli-Grid Crimp Terminal, Chain, 0.38µm Select Gold, 28-22 AWG, Lead-Free	873968051
1.50mm Pitch NSCC, Wire-to-Wire, Receptacle Housing, Black, 8 Circuits	987881081
1.50mm Pitch NSCC, Wire-to-Wire, Receptacle Housing, Gray, 10 Circuits	987881201
1.50mm Pitch NSCC, Wire-to-Wire, Receptacle Housing, Gray, 8 Circuits	987881088
1.50mm Pitch NSCC, Sealed Female Housing, 10 Circuits, Dual Row, White	987881208
NSCC single part Non Sealed, 1.50mm, Male Housing, 10 Circuits, Dual Row, Black	987891081
NSCC Single Part, Unsealed, 1.50mm, Male Housing, 10 Circuits, Dual Row, Black	987891201
NSCC single part, Non Sealed, 1.50mm, Male Housing, 10 Circuits, Dual Row, Gray	987891088
NSCC Single Part, Non-Sealed, 1.50mm, Male Housing, 10 Circuits, Dual Row, Gray	987891208
2.00mm Pitch EdgeLock Crimp Terminal, Phosphor Bronze, Tin (Sn) Plating,Reel	2004490001

Downloaded from Arrow.com.