




Part Number : [2257725314](#)
Product Description : HSAutoLink II Unsealed Plug-to-HSAutoLink II Unsealed Plug Off-the-Shelf (OTS) Cable Assembly, High-Bandwidth LVDS 2-Pair Cable, 2.0m Length, Polarization A, 12 Circuits
Series Number : 225772
Status : Active
Product Category : Power and Signal Cable Assemblies



Documents & Resources

- Drawings**
[2257725314 sd.pdf](#)
- Specifications**
[2257721200-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Reviewed
China RoHS	Not Relevant
EU ELV	Not Reviewed per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

- Compliance Statements
- EU RoHS
 - REACH SVHC
 - Low-Halogen

- Industry Documents
- IPC 1752A Class C
 - IPC 1752A Class D
 - Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	225772
Description	HSAutoLink II Unsealed Plug-to-HSAutoLink II Unsealed Plug Off-the-Shelf (OTS) Cable Assembly, High-Bandwidth LVDS 2-Pair Cable, 2.0m Length, Polarization A, 12 Circuits
Application	Automotive, Wire-to-Board, Signal, Power
Assembly Configuration	Dual Ended Connectors
Connector to Connector	HSAutoLink II-to-HSAutoLink II
Product Name	HSAutoLink II
Type	Discrete Wire Assembly
UPC	198282474647

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	36V

Physical

Cable Length	2.0m
Circuits (Loaded)	12
Circuits (maximum)	12
Color - Resin	Black
Gender	Male-Male

Lock to Mating Part	Yes
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	115.000/g
Number of Rows	2
Packaging Type	Carton
Pitch - Mating Interface	1.27mm
Single Ended	No
Wire/Cable Type	High-Bandwidth LVDS 2-Pair
Wire Size (AWG)	28

Mates With / Use With

Mates with Part(s)

Description	Part Number
HSAutoLink II Unsealed Header, Right-Angle, 12 Circuits, Key A, Black	<u>2257701016</u>
HSAutoLink II Unsealed Header, Vertical, 12 Circuits, Key A, Black	<u>2257702016</u>

This document was generated on Oct 05, 2025