

Product Line

- [DeepTronica](#) >
- [Single Pair Ethernet](#) >
- [ZConnect](#) >
- [Ceres](#) >
- [X-Lok](#) >
- [M Series](#) >
- [FLDS & FLDS+](#) >
- [Power](#) >
- [RBL](#) >
- [HS-Lok](#) >
- [NMEA 2000](#) >
- [Heavy Duty Shielded](#) >
- [RJ](#) >
- [USB](#) >
- [SSL](#) >
- [HDMI](#) >
- [DVI](#) >
- [Fiber Optic](#) >
- [RF](#) >
- [Cable Joiner](#) >
- [Cable Gland](#) >
- [Pressure Relief Vent](#) >
- [LED Light Guide](#) >
- [D-Sub](#) >



M12A-12PFFP-SF8002

Operating Temperature: -40°C ~ +105°C
 Transmission Speed: N/A
 Shielded: Metal, Non-shielded
 Jacket Material: N/A
 Certificate: UL1977, UL2238, UL1863

You must login first for view the price

Quantity

[Check Stock](#)

[Add to Cart](#)

[Inquiry](#)

[Heart icon](#)

Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type [Search](#)

APPM-A12MAPAN-AS1
M Series, M12, A Code, Metal...

CAP-WBDFSA1
M Series, Accessorv...

CAP-WBDFSA2
M Series, Accessorv...

CAP-WBDFSPB1
M Series, Accessorv...

[Add to Cart](#) [Inquiry](#)

Specifications	Download / CAD
Nominal Current 1.5A	Connector Type Receptacle
Shielded Metal, Non-shielded	No. of Contacts 12
Connector Gender Female	Backshell Hexagonal
Mating Style Screw Thread	IP Rating IP68
Assembly Style PCB 180°	
Operating voltage 30V	Operating Temperature -40°C ~ +105°C
Coding A	Contact Gender Female
Receptacle Nut Thread M16*1.5	Fasten Style Front
Wire/Cable Length N/A	Air Permeability N/A
Cable O.D N/A	Wire AWG N/A
Panel Thickness 4.50	
More Options	

People Also Bought

M12A-12PFFP-SF8002

BBD-06AFMM-QL8F10

8-03BMMM-SR7B03

MSAP06ML-SAPMR-..

CBU-08PMES-TC7001