

CH3M, Cable Tie Hanger

By Burndy
Catalog # CH3M

Nylon Cable Hanger



Features

- Cable hangers provide a contact area range of 1/2" to 3/8" in width
- All contact edges have a full radius for product protection
- Sizes clearly marked on each clamp

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No
Certification - UV Rated	No

Configuration

Mounting Method	Screw
-----------------	-------

Dimensions

Dimension - Width inch	0.38 in
Package Length	0.000 in

Dimension - Width mm	10 mm
Package Width	0.000 in
Package Weight	0.000 lb.
Package Height	0.000 in
Dimension - Bundle Diameter Max inch	.21

General

Trade Name	UNIRAP™
Color	Natural
UPC 14 Digit GTIN	00781810336137
Material	NYLON 6/6
UPC	781810336137

Logistics

Minimum Pack Quantity	1000
Packaging Type	Bag
Carton Quantity	1000
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)