

Loading...

50ft RG58 BNC Thinnet Coax Cable

The ideal cable for ThinNet Ethernet 802.3 network applications

★★★★★

4.7

7 Reviews

Product # : 03189

Connector 1 : (1) BNC Male


Connector 2 : (1) BNC Male

Lengths :

50ft8ft15ft25ft75ft

Roll over image to zoom in

171 In Stock & ready to ship!



Need it shipped today?
Place your order before the timer runs out!

09: 24: 53

print share chat

- Product Info
- ★ Customer Reviews
- Questions & Answers
- Distributors
- More Choices

- Description
- Certifications
- Specs

Product Description

This heavy duty cable will stand the test of time in the toughest environments. It meets or exceeds standards for shielding and features a rugged design. BNC cables are the solution in environments where there is considerable interference, or where running new twisted pair wire is not feasible.

WARNING: Cancer and Reproductive Harm www.P65Warnings.ca.gov

Product Certifications



Product Specifications

Color :	Black
Length :	50.00 Foot
UPC :	757120031895
Warranty :	Lifetime

Weight :

1.320 LB

For more detailed specifications, please [read this](#).

- Impedance: 50 Ohm

System Requirements

- Requires BNC t-connector for proper connection at nic or hub

Info

- About Us
- Order History
- Where To Buy
- More ▾

Service

- Contact Us
- OEM Solutions
- Tech Support
- More ▾

Resources

- Connector Guides
- ConnectXpress
- Drivers & Manuals
- More ▾

Have A Question?

- Get help with [Chat](#)
- Call C2G **800.506.9607**
- [f](#) [t](#) [v](#) [b](#)



United States | Europe +

Copyright © 2019 C2G. All Rights Reserved

