



UNIT: mm




CABLE BLACK PRINT
USB CABLE E189529 AWM 2725 28AWG/1PR AND
24AWG/2C 80°C 30V VW-1

PIN ASSIGNMENT:



Electrical test:
1. 100% short, open, miswire test
2. Conduct resistance: 2 Ohm(max)
3. Insulation resistance: 10Mohm(min)
4. dielectric test: DC 300V



1PCS/PE BAG

⑨	PE BAG	1/10	CLEAR SIZE: 280*330*0.05mm PRINT BLACK "MADE IN CHINA" + "10PCS"
⑧	PE BAG	1	CLEAR SIZE: 130*230*0.05mm PRINT BLACK "MADE IN CHINA"
⑦	TIE	2	WHITE L=100mm
⑥	IN JACKET	3g	CLEAR LDPE (MOULD NO: NM-027)
⑤	OUT JACKET	7g	BEIGE (IV-29#) PVC-40P (MOULD NO: WM-83)
④	OUT JACKET	6g	BEIGE (IV-29#) PVC-40P (MOULD NO: WM-40)
③	CABLE	1	BEIGE (IV-29#) USB1.1 UL2725 28#/1P+24#/2C+AEB OD: 4.7mm L=3000 ± 10mm
②	CONN	1	USB A FEMALE SHELL: NICKEL PIN G/F SHORT TYPE INSULATOR COLOR: WHITE
①	CONN	1set	USB A MALE SHELL: NICKEL PIN G/F 3PCS TYPE INSULATOR COLOR: WHITE
NO.	NAME	QTY	SPECIFICATION

CNC Tech, LLC
Industrial Cable and Connector Technology

DRAWN	Andy	DRAWING NO	
CHECKED		CUSTOMER	
APPROVAL		ITEM NO.	101-1010-BE-00300
DECIDED		DATE	2013-8-23
VERSIONS/EDITION	A/0	PROJECTION	

