Part Number : 733910321
Product Description : SMA Jack, Reverse Polarity, Right-Angle, PCB Receptacle, Die Cast Body, Nickel (Ni) Plated, 50 Ohms
Series Number : 73391
Status : Active
Product Category : RF / Coaxial Connectors



Documents and Resources

Drawings

733910321_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

Downloaded from Arrow.com.

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73391
Description	SMA Jack, Reverse Polarity, Right-Angle, PCB Receptacle, Die Cast Body, Nickel (Ni) Plated, 50 Ohms
Application	RF
Product Name	SMA
Style	PCB
Type	Subminiature
UPC	887191214207

Electrical

Frequency	18 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 500 Vrms@Sea Level

Physical

Cable Attachment	N/A
Gender	RP Jack
Keying to Mating Part	N/A
Net Weight	3.197/g
Orientation	Right Angle
Packaging Type	Tray
Panel Mount	No

Downloaded from Arrow.com.

Panel Mount Method	N/A
PCB Mounting	Through Hole
PCB Thickness - Recommended	3.81mm
Reverse Polar	Yes
Wire/Cable Type	N/A

Downloaded from Arrow.com.