

## Component housing - HS LC-H-D2/ R2XC4-2,54 - 2202531

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Fiber optics can be used for the ME, ME-MAX, ME-IO, ME PLC, and EH housing ranges (housing must be processed), Color: transparent

**RoHS**

### Key Commercial Data

Packing unit	1 STK
Minimum order quantity	100 STK
GTIN	 4 055626 149134
GTIN	4055626149134
Custom tariff number	39269097
Country of origin	Tunisia

### Technical data

#### General

Housing type	Fiber optics
Housing material	PC
Color	transparent

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
---------------------------------	------------------

#### Dimensions

Pitch	2.54 mm
-------	---------

#### Technical data

Flammability rating according to UL 94	HB
Number of positions	8

## Component housing - HS LC-H-D2/ R2XC4-2,54 - 2202531

### Technical data

#### Standards and Regulations

Flammability rating according to UL 94	HB
--	----

#### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

### Classifications

#### eCl@ss

eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

#### ETIM

ETIM 5.0	EC001031
ETIM 6.0	EC001031

#### UNSPSC

UNSPSC 13.2	31261501
-------------	----------