

NOTES:

1. MATERIAL:

- A. BODY; PHOSPHOR BRONZE PER QQ-B-750.
- B. SCREW; STAINLESS STEEL PER QQ-S-763, 100 SERIES.
- C. CLAMP INSERT; FLUOROSILICONE ELASTOMER PER MIL-R-25988.

2. FINISH:

- A. BODY; TIN PLATED PER MIL-T-10727 OVER NICKEL PER MIL-C-26074.
- B. SCREW; PASSIVATED PER QQ-P-35.




3. THESE DIMENSIONS ARE FOR MAXIMUM CABLE ACCOMMODATION.

- 4. Raychem PART NUMBER CHA-0016. IS MARKED ON BACKSHELL PACKAGE.

- 5. THIS BACKSHELL IS FOR USE WITH Raychem MTC COAX CONNECTORS. 1" COAX PLUG OR 1" COAX RECEPTACLE AS SHOWN.

6. .125 DIA. MAX. (CONSTRUCTION HOLES) TWO (2) HOLES ON EACH HALF OF PART APPROX. AS SHOWN.

REVISIONS		DATE	APPROVED
ZONE	LTR	DESCRIPTION	
1	A	REVISED PER ECN F-012650	



CONNECTOR SPECIFICATION CONTROL DRAWING

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES BRACKETED DIMENSIONS () ARE METRIC AND TOLERANCES ARE: XXX: ± — (—) XX: ± — (—) Δ: ± —	DRAWN	WJACKSON	9-30-80	Raychem RAYCHEM CORPORATION 330 CONSTITUTION DRIVE MENLO PARK, CALIFORNIA 94025
	CHECKED	JB		
	APPROVED	Plain	9-30-80	
	APPROVED			
	APPROVED			TITLE RIGHT ANGLE BREAKOUT BACKSHELL ASSY 1 INCH MTC COAX
DO NOT SCALE THIS DRAWING	SIZE	C	CODE IDENT	DWG. NO.
			NO. 06080	CHA-0016
	WEIGHT		SHEET	OF 1

If this document is printed it becomes uncontrolled.
Check with the web for latest revision.