
Part Number : 2196552113
Product Description : Pre-Crimped Lead Micro-One Female-to-Pigtail, Matte Tin Plating, 225.00mm Length, 24 AWG, Red
Series Number : 219655
Status : Active
Product Category : Power and Signal Cable Assemblies



Documents and Resources

Drawings

2196552113_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	219655
Description	Pre-Crimped Lead Micro-One Female-to-Pigtail, Matte Tin Plating, 225.00mm Length, 24 AWG, Red
Application	Wire-to-Board
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Micro-One-to-Pigtail
Product Name	Micro-One
UPC	195842804043

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC (RMS)/DC

Physical

Cable Length	225.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Red
Gender	Female-Pigtail
Material - Metal	Copper Alloy
Material - Plating Mating	Matte Tin
Net Weight	0.972/g
Packaging Type	Bag
Plating min - Mating	0.900µm
Plating min - Termination	0.900µm
Single Ended	Yes

Downloaded from Arrow.com.

Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1569
Wire Size (AWG)	24

Mates With / Use With

Use with Part(s)

Description	Part Number
Micro-One Wire-to-Board Receptacle Housings	205979
Micro-One Single Row Receptacle Housings	212724

Downloaded from Arrow.com.