

Mini DisplayPort 1.2 to DVI Active Adapter Cable (M/M), 1080p, 3 ft. (0.9 m)

MODEL NUMBER: **P586-003-DVI-V2**



Converts a Mini DisplayPort v1.2 video signal for display on a DVI monitor, projector or television.

Features

Send High-Quality Mini DisplayPort v1.2 Video Signals to a DVI Display

- Connects Mini DisplayPort (or Thunderbolt) computer to DVI-enabled monitor, projector or TV
- Ideal for displaying video on large monitor or digital sign
- Mini DisplayPort and DVI-D male connectors
- No separate adapter required

Vibrant, Superior Video Quality

- Supports HD video resolutions up to 1920 x 1080 (1080p)
- Converts Single-Mode and Dual-Mode (DP++) Mini DisplayPort output
- Perfect for use with graphics cards, such as AMD Eyefinity, that don't output DP++ signals

Superior Materials for Superior Performance

- Double shielding with foil and braid for maximum EMI/RFI protection
- Gold-plated connectors and contacts for excellent conductivity
- Integral strain relief for long life

Specifications

OVERVIEW	
UPC Code	037332192004
Product Type	Active
Technology	DVI; DisplayPort

Highlights

- Active adapter cable for use with any Mini Displayport (or Thunderbolt) port
- Supports HD video resolution up to 1920 x 1080 (1080p)
- No separate adapter required
- Gold-plated connectors and contacts

Package Includes

- P586-003-DVI-V2 Mini DisplayPort 1.2 to DVI Active Adapter Cable, 3 ft.

VIDEO	
Max Supported Video Resolution	1920 x 1080 (1080p)
Max Supported Color Depth	12-bit True Color
HDR Support	No
Chroma Sub Sampling	4:4:4; 4:2:2
PHYSICAL	
Material of Construction	ABS, PVC
Color	Black
Cable Jacket Color	Black
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	4.8mm
Wire Gauge (AWG)	32
Cable Length (ft.)	3
Cable Length (m)	0.91
Cable Length (in.)	36
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.10
Shipping Weight (lbs.)	0.21
ENVIRONMENTAL	
Operating Temperature Range	32 to 113 F (0 to 45 C)
Storage Temperature Range	14 to 176 F (-10 to 80 C)
Operating Humidity Range	10 to 85%, Non-Condensing
Storage Humidity Range	5 to 90%, Non-Condensing
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	DVI-D DUAL-LINK (MALE) (WIRED TO DVI-D SINGLE-LINK)
Connector Plating	Gold
Contact Plating	Gold
Latching or Gripping Connector	No
FEATURES & SPECIFICATIONS	
Displayport Specification	1.2



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

HDCP Specification	1.4
IP68 Rated	No
STANDARDS & COMPLIANCE	
Certifications	CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty
Product Warranty Period (U.S. & Canada)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>