Part Number : 732870630
Product Description : 2.92mm Termination, Plug, Straight, 40 GHz, 1 Watt, without Chain
Series Number : 73287
Status : Active
Product Category : RF / Coaxial Connectors



Documents and Resources

Drawings

732870630_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Downloaded from Arrow.com.

- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73287
Description	2.92mm Termination, Plug, Straight, 40 GHz, 1 Watt, without Chain
Application	RF
Keyword	Termination, Terminations
Product Name	2.92mm,Termination
Style	Coaxial Termination
Type	Subminiature
UPC	198282628699

Electrical

Average Power Max (Watts)	1
Frequency	40 GHz
Impedance	50Ω
VSWR (max)	1.20:1

Physical

Body Style	Without Chain
Cable Attachment	N/A
Gender	Plug
Keying to Mating Part	N/A
Orientation	Straight
Packaging Type	Bag
Panel Mount	No

Downloaded from Arrow.com.

Panel Mount Method	N/A
PCB Mounting	N/A
Reverse Polar	No
Wire/Cable Type	N/A

Downloaded from Arrow.com.