



+ CONNECTORS
HOUSINGS



✓ Active

TE CONNECTIVITY (TE)
15P LOCKG CLIP GEH
AMP | AMPMODU

1-926657-5
TE Internal Number: 1-926657-5

EU RoHS Compliant
EU ELV Compliant

Centerline (mm) 2.54
Termination Method to Wire/Cable Crimp
Centerline (Pitch) (in) .1
Number of Rows 1
Row-to-Row Spacing 2.54 mm [.1 in]

↓ PRODUCT DRAWING
English

↓ 3D PDF

DOCUMENTATION

Product Drawings
Locking Clip Housing
PDF (TIFF AVAILABLE)
English

CAD Files
Customer View Model
3D_IGS.ZIP
English

Customer View Model
3D_STP.ZIP
English
Customer View Model

2D_DXF.ZIP

English

3D PDF

PDF

English

Agency Approvals

Agency Approval Document

AMPMODU CONNECTOR REPORT (GERMANY)

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Row-to-Row Spacing 2.54 mm [.1 in]

Strain Relief Without

Connector Type Housing

Connector Style Receptacle

Product Type Connector

Configuration Features

Number of Rows 1

Number of Positions 15

Stamped No

Body Features

Color Black

Contact Features

Contact Type Socket

Termination Features

Termination Method to Wire/Cable Crimp

Mechanical Attachment

Mating Retention Without

Mating Connector Lock Without

Mating Alignment Without

PCB Mount Retention Without

Housing Features

Centerline (mm) 2.54
Centerline (Pitch) (in) .1
Housing Material PBT GV15
Housing Color Black
Housing Configuration Both Ends Closed

Operation/Application
For Use With Plug

Industry Standards
UL Flammability Rating UL 94V-0

Packaging Features
Packaging Method Carton
Packaging Quantity 1000

Statement of Compliance
Statement of Compliance
PDF