

## Han 3EMC-Base angled-M25



Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 19 62 003 1165  |
| Specification      | Han 3EMC-Base angled-M25  |
| HARTING eCatalogue | <a href="https://harting.com/19620031165">https://harting.com/19620031165</a> |

### Identification

|                             |                       |
|-----------------------------|-----------------------|
| Category                    | Hoods / Housings      |
| Series of hoods/housings    | Han <sup>®</sup> EMC  |
| Type of hood/housing        | Screw mounted housing |
| Description of hood/housing | Angled                |

### Version

|                         |  |
|-------------------------|--|
| Size                    | 3 A  |
| Number of cable entries | 1  |
| Cable entry             | 1x M25                                     |
| Locking type            | Single locking lever                       |
| Field of application    | Hoods/Housings for higher EMC requirements |
| Pack contents           | Please order seal screw separately.        |

### Technical characteristics

|  |  |
|--|--|
| Limiting temperature                   | -40 ... +125 °C                                      |
| Note on the limiting temperature       | For use as a connector according to IEC 61984.       |
| Degree of protection acc. to IEC 60529 | IP44<br>IP65 With seal screw<br>IP67 With seal screw |
| Type rating acc. to UL 50 / UL 50E     | 12   |

### Material properties

|                         |               |
|-------------------------|---------------|
| Material (hood/housing) | Zinc die-cast |
| Surface (hood/housing)  | Uncoated      |



**Pushing Performance**  
 Since 1945

## Material properties

|                                      |  |
|--------------------------------------|--|
| Colour (hood/housing)                | Unpainted  |
| Material (locking)                   | Steel  |
| Surface (locking)                    | Zinc plated  |
| RoHS                                 | compliant with exemption   |
| RoHS exemptions                      | 6(a)-I: Lead as an alloying element in steel for machining purposes containing up to 0,35 % lead by weight<br>6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status                           | compliant with exemption   |
| China RoHS                           | 50   |
| REACH Annex XVII substances          | Not contained  |
| REACH ANNEX XIV substances           | Not contained  |
| REACH SVHC substances                | Yes  |
| REACH SVHC substances                | Lead   |
| California Proposition 65 substances | Yes  |
| California Proposition 65 substances | Lead<br>Nickel   |

## Specifications and approvals

|           |              |
|-----------|--------------|
| Approvals | CE<br>DNV GL |
|-----------|--------------|

## Commercial data

|                                |  |
|--------------------------------|--|
| Packaging size                 | 10                                       |
| Net weight                     | 81.5 g                                   |
| Country of origin              | Germany                                  |
| European customs tariff number | 85389099                                 |
| GTIN                           | 5713140171459                            |
| eCl@ss                         | 27440202 Shell for industrial connectors |
| ETIM                           | EC000437                                 |
| UNSPSC 24.0                    | 39121466                                 |