


REV.	DATE	ECR NO.	DESCRIPTION
NC	06/03/99	—	INITIAL RELEASE
A	01/12/09	—	UPDATE DRAWING FORMAT



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex PART DESCRIPTION BNC TERMINATOR JACK – 50ohm 1 WATT – 5%							
8						DRAWN	GRS	01/12/09									
7						CHECKED											
6						ISSUED				PART NO. 202120							
5						SHEET	1 OF 1										
4	COVER	BRASS	NICKEL	1													
3	CONTACT PIN	PHOS. BRONZE	GOLD	1						PART NO. 202120							
2	INSULATOR	PTFE	NATURAL	1													
1	BODY	BRASS	NICKEL	1													
	DESCRIPTION	MATERIAL	FINISH	QTY		CAD FILE				DWG. NO.		202120.DWG	REV.	A	SIZE	A	SCALE
					C:/202/202120.DWG												