

LUMAWISE ALR SHORTING AND OPEN CAPS

DURABLE, WEATHERPROOF, LONG LASTING

TE Connectivity (TE) offers durable weatherproof LUMAWISE ALR shorting and open caps that provide harsh environmental protection to roadway, street and area lighting luminaires. Shorting caps are commonly used to protect NEMA twist lock receptacles on outdoor luminaires prior to the installation of a discrete or network lighting control. Other uses include designating lighting fixtures for maintenance, keeping lights on continually for safety or using an open cap to disconnect service.

LUMAWISE ALR Series shorting and open caps are IP54 weatherproof rated. The ALR-MC-10 shorting cap with an integrated 545 Joule Metal Oxide Varistor (MOV) provides protection against transient line surges for LED luminaires.

Part descriptions that include ANSI provide a unit with a stepped housing as referenced in the ANSI C136.10 specification. This unique housing makes it easier for users to distinguish visually between a standard photocontrol and a shorting or open cap.



PROVIDES A SAFE, CONVENIENT AND ECONOMICAL METHOD TO CLOSE OR OPEN THE PRIMARY CIRCUIT PATH ACROSS A NEMA TWIST LOCK RECEPTACLE ON AN OUTDOOR LIGHTING LUMINAIRE. THE LUMAWISE ENDURANCE N ALR SHORTING AND OPEN CAPS ARE C136.10 COMPLIANT AND UL LISTED.

FEATURES:

- ANSI C136.10 compliant
- IP54 weatherproof rating
- Distinct cap shape improves visual distinction between standard photo controls and shorting caps
- Optional surge
- protection (545 Joule)

APPLICATIONS:

- Street and area lighting
- Roadway lighting
- Commercial outdoor lighting (i.e. parking lots, car dealerships)

LUMAWISE ALR SHORTING AND OPEN CAPS

DURABLE, WEATHERPROOF, LONG LASTING

ELECTRICAL:

- **Current rating:** 15 A Max
- **Voltage rating:** 0 – 480 Max

MECHANICAL:

- **Operating temperature rating:**
-40° C to +65° C at 96% RH

SPECIFICATIONS:

- ANSI C136.10
- cUL Listed: E66375

MATERIALS:

- **Cover:** High impact polypropylene (ANSI Series)
- High impact UV stabilized polycarbonate (SC-10A Series)
- **Base:** High temperature polyester (PBT)
- **Gasket:** Cross-linked polyethylene
- **Connection:** 3 pole locking-type with solid brass legs

PRODUCT SELECTION INFORMATION

Part Number	ALR PN Description	Circuit Type	Cap Color	Load Rating Tungsten (Watts)	Load Rating Ballast (VA)	Surge Protection (Joules)	Housing Dimensions
D02595-000	ALR-SC-10A*	Shorting	Clear	1000	1800	-	2.87 (73mm) Dia. X 1.61 (41mm) Height
8Q526Y-000	ALR-SC-10ANSI**	Shorting	Black	1000	1800	-	2.87 (73mm) Dia. X 1.40 (35.56mm) Height
5J5271-000	ALR-MC-10ANSI**	Shorting	Black	1000	1800	545	2.87 (73mm) Dia. X 1.40 (35.56mm) Height
J2745D-000	ALR-NS-10ANSI**	Open	Red	1000	1800	-	2.87 (73mm) Dia. X 1.40 (35.56mm) Height

* UL Listed

** ANSI C136-10-2006 Compliant



te.com

© 2021 TE Connectivity. All Rights Reserved.

LUMAWISE, TE Connectivity, TE connectivity (logo) and Every Connection Counts are trademarks owned or licensed by TE Connectivity. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

05/21 AK