



*Quality Products. Service Excellence.*

## Hospital-Grade Outlet Strip 1584H Series

15A | 125V | 5-15R-HG Outlets

### Features



- Featuring a sturdy aluminum extruded case with a distinctive black powder paint coated steel cover.
- Designed to meet the special requirements for institutional and chronic care use with "Hospital Grade" white receptacles, line cord and plug.
- These devices are intended for non-patient connected indoor applications to providing power to electronic equipment.
- These devices are not intended to be used to supply power to life-support appliances, and not for use in critical care environments.
- Exceeds NEMA requirements for low leakage ground return and for withstanding impact or continuous physical shock without loss of grounding path continuity when plugged into properly grounded source receptacles.
- The white "Hospital Grade" receptacles are securely fastened onto the housing and interconnected with solidly bonded bus bars. All bus bars are double connected with a convection pressure sensitive clamp and safety screw.
- **Perfect for ground sensitive audio applications!**
- An additional grounding stud is provided on the case for any further external grounding requirements.
- Mounting feet (with keyhole slots) allow temporary work station mounting if desired.

### Specifications

- Heavy duty 14 gauge cord - 14/3 SJT for extreme temperature ranges and integral clear molded "Hospital Grade" plug.
- Receptacles are NEMA 5-15R-HG.
- Complete with a 15 amp, 125 volt resettable circuit breaker to prevent accidental line overload.
- CSA certified, Standards C22.2 No. 308-18 Class 5842 08 (Hospital Grade Powerbars).
- TUVus certified to ANSI ES60601-1 (Medical Grade) & UL1363/1363A (Medical Grade) RPT's.
- TAA compliant for GSA Schedule purchases.
- RoHS Compliant.
- Manufactured in North America.

### Accessories

- Rack Cabinet Vertical Mount Adaptor

| Part No.  | Overall Dimensions |       |        | Cord    |             |
|-----------|--------------------|-------|--------|---------|-------------|
|           | Height             | Width | Length | Outlets | Length (ft) |
| 1584T4DH6 | 2.33               | 2.12  | 10.18  | 4       | 6           |
| 1584T4DH  | 2.33               | 2.13  | 10.18  | 4       | 12          |
| 1584T6DH6 | 2.33               | 2.12  | 13.36  | 6       | 6           |
| 1584T6DH  | 2.33               | 2.13  | 13.36  | 6       | 12          |

| Overall Dimensions |        |       |        |         | Cord        |
|--------------------|--------|-------|--------|---------|-------------|
| Part No.           | Height | Width | Length | Outlets | Length (ft) |
| 1584T8DH6          | 2.33   | 2.12  | 16.51  | 8       | 6           |
| 1584T8DH           | 2.33   | 2.13  | 16.51  | 8       | 12          |

Replacement Mounting Foot (One Foot)

|          |        |
|----------|--------|
| Part No. | 1584MF |
|----------|--------|

Data subject to change without notice

© 2025. Hammond Manufacturing Ltd. All rights reserved.