

UTP28SP5GR

Category 6 Performance, 28 AWG UTP patch cord with TX6™ Modular Plugs on each end. Green, 5 ft.

Specs | Packaging Details | Documents

Add to Favorites | Add to BOM

Conductor Gauge (AWG)	28
Performance Level	Category 6
Conductor Type	Stranded
Overall Length (ft.)	5
Overall Length (m)	1.5
Maximum Operating Temperature (°C)	75
Maximum Operating Temperature (°F)	167
Minimum Operating Temperature (°C)	-10
Minimum Operating Temperature (°F)	14
Maximum Storage Temperature (°C)	70
Maximum Storage Temperature (°F)	158
Minimum Storage Temperature (°C)	-40
Minimum Storage Temperature (°F)	-40
Flammability Rating	CM, LSZH-1 (60332-1)
Standards Met	IEEE 802.3af, 802.3at, 802.3bt type 3 and type 4, UL 1863.
Cable Type	U/UTP
Cable Color	Green
Length (ft.)	5.00
Termination End 1	Modular Plug
Termination End 2	Modular Plug
CE Compliant	Yes
Nominal Cable Outside Diameter (In.)	0.15
Nominal Cable Outside Diameter (mm)	3.8
Boot Color	Clear
Cable Length (ft.)	5.00
Conductor Material	Copper
Material	Copper

Downloaded from Arrow.com.

Maximum Installation Temperature (°C)	70
Maximum Installation Temperature (°F)	158
Minimum Installation Temperature (°C)	-40
Minimum Installation Temperature (°F)	-40
Part Features	100% performance tested for wire map, NEXT and return loss, Centered de-embedded plug, Integral pair manager, Patented tangle-free latch
RoHS Compliancy Status	Compliant
Min. Order Qty.	1

Downloaded from Arrow.com.