

NOTES:

- 1. SIDE GLOW LIGHT PIPE AND ADAPTER ASSEMBLY SHIPPED UNASSEMBLED.
- 2. LENGTHS AVAILABLE FROM 6.0IN [152mm] UP TO 36.0IN [914mm].
- 3. SIDE GLOW LIGHT PIPE INSERTED INTO ADAPTER HOUSING TO COMPLETE INSTALLATION.
- 4. RECOMMENDED FOR ONE TIME INSERTION.

PART NUMBER CONFIGURATOR





TABLE 1 - LENGTH	
LENGTH (L)*	TOLERANCE
6.0" - 16.0"	±0.1"
16.1" - 36.0"	±0.2"

TABLE 2 - LED	
ORDER CODE	COLOR
RGB	RGB

*AVAILABLE IN 0.1" INCREMENTS



REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
D	UPDATED BOM	7/17/2024	A.V.
E	UPDATED BOM	7/31/2024	A.V.
F	UPDATED MFG DRAWING	8/12/2024	A.V.
G	ECO-1300: UPDATED PCBA BOM	10/24/2024	A.V.
H	ECO-1316: REMOVED HEAT SHRINK	2/20/2025	A.V.







TABLE 3 - LED SOURCE INFORMATION			
Emitted RGB Colors	Dom. Wave L.	Electro-Optical Data	
	λ_p [nm]	V_f [V]	I_v [mcd]
	TYP	TYP	TYP
Red	622	5.0	550
Green	525	5.0	4500
Blue	465	5.0	500

CABLE DESIGNATION	
CABLE COLOR	DESCRIPTION
BLACK	+5V
RED	RED LED
GREEN	GREEN LED
BLUE	BLUE LED



DETAIL A
SCALE 4 : 1

CUSTOMER USE DRAWING

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		BIVAR [®] 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
DECIMALS	ANGULAR		
.X ± .1	X° ± 1°	TITLE: SURFACE AREA LIGHT GUIDE, SIDE GLOW 3mm	
.XX ± .02		DRAWING NO: SASG3-YY.YY-ZZZ	REVISION: H
.XXX ± .010		SHEET SIZE A	CAGE CODE: 32559
DESIGNED: K. BARON	DATE: 6/5/2024	SCALE: 1:1	SHEET # 1 OF 1
REVISED: K. BARON	DATE: 2/20/2025	CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING	
CHECKED: D. ASHBY	DATE: 2/20/2025		