



REVISIONS

4G46PI GIGABIT CIRCUIT△△




C2 - C5 = 0.1uF, 50V, CAPACITOR
C1 = 1000pF, 2KV, CAPACITOR
R1 - R4 = 75 ohms, RESISTOR






SUGGESTED PCB LAYOUT(TOL:±0.05)
(COMPONENT SIDE VIEW)

SINGLE COLOR LED



BI-COLOR LED



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TOMMY REN 18AUG2006		 trp CONNECTOR a bel group		DONGGUAN CHINA	
		CHK KEITH ZHU 18AUG2006					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD TEDDY XIONG 18AUG2006		DESC IXI, MAGJACK, VERTICAL 4G46PI, GIGABIT CIRCUIT, W/ LEDS	
		0 PLC ±0.25 1 PLC ±0.25 2 PLC ±0.25 3 PLC ±0.25 4 PLC ± ANGLES ±		MODEL NAME MAGJACK SINGLE NON-POE		SIZE A2	
PRODUCT SPEC 108-2100		APPLICATION SPEC -				DRAWING NO C=1840417	
				CUSTOMER DRAWING		RESTRICTED TO -	
						SCALE 4:1	
						SHEET 2 OF 2	
						REV E	