

Search within category

GO

BUY NOW

DESIGN / INSTALL



STP28X7MBU

Category 6A Performance, 28AWG, F/UTP Patch Cord, CM/LSZH, Blue, 7m.

Specs	Packaging Details	Documents	★ Add to Favorites	🛒 Add to BOM
Performance Level	Category 6A			
Cable Color	Blue			
Length (ft.)	22.97			
Length (m)	7.0			
Flammability Rating	CM, LSZH-1 (60332-1)			
Termination End 1	Modular Plug			
Termination End 2	Modular Plug			
Standards	IEEE 802.3af, 802.3at, 802.3bt type 3 and type 4, UL 1863.			
CE Compliant	Yes			
Nominal Cable O.D. (In.)	0.19			
Nominal Cable O.D. (mm)	4.7			
Operating Temperature	14°F to 140°F (-10°C to 60°C)			
Storage Temperature	-40°F to 158°F (-40°C to 70°C)			
UL5A Listed	No			
AWG Size	28			
BMEcat - Type of Connector	RJ45 8(8)			
Cable Type	F/UTP			
Conductor Material	Copper			
Installation Temperature	-40°F to 158°F (-40°C to 70°C)			
RoHS Compliancy Status	Compliant			
Min. Order Qty.	1			