





OBSOLETE



PRODUCT SPECIFICATION -108-25020 (MOD IV STANDARD CONTACT PRESSURE)
 -108-25021 (MOD IV INTERMEDIATE CONTACT PRESSURE)
 -108-25007 (MOD V HIGH CONTACT PRESSURE)



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 29AUG2019 KARTHIK JK		 TE Connectivity	
		CHK 29AUG2019 HARI SURIYA			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2mm		NAME AMPMODU IV RECEPTACLE HOUSING DUAL ROW, WITH STRAIN RELIEF -	
		APVD 29AUG2019 PRASHANTH S PRODUCT SPEC			
0 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		APPLICATION SPEC 114-25003			
MATERIAL PA66 GREEN RAL 6001		FINISH - -			
		WEIGHT -		SIZE A2	
				CAGE CODE 00779	
				DRAWING NO C=925370	
				RESTRICTED TO	
		CUSTOMER DRAWING		SCALE 5:1	
				SHEET 1 of 1	
				REV AA	