

151-00367

HellermannTyton



Article Number: 151-00367

Description: Automatic Harness Clips - Non-Connectable Push Mount
Max Bun Dia .79" Black 900 /Pkg

Base Data		
	Local Order Number	151-00367
	Type	AHC2AH
	Color	Black (BK)
	Features and benefits	These clips offer a simple and secure method of attaching cables to panels. They can be attached to the panel prior to installing the cables. Simply pushing the cable into place closes the clip and activates the automatic locking feature.
	Quantity Per	carton
	Product Description	Offering a simple and secure method of attaching cables to panels. Originally designed for the automotive industry, these products are used in a wide range of applications with sheet metal panels across various industries.
	GLOBAL PART NAME	AHC2AH-PA66HIRHS-BK
Product Dimensions	Short Description	Automatic Harness Clips - Non-Connectable Push Mount Max Bun Dia .79" Black 900 /Pkg
	Length L (Imperial)	1.16"
	Length L (Metric)	29.5mm
	Length L2 (Imperial)	0.28"
	Length L2 (Metric)	7.0mm
	Width W (Imperial)	0.39"
	Width W (Metric)	10.0mm
	Bundle Diameter Min. (Imperial)	0.43"
	Bundle Diameter Min. (Metric)	11.0mm
	Bundle Diameter Max. (Imperial)	0.79"
	Bundle Diameter Max. (Metric)	20.0mm
	Disc Diameter (Imperial)	0.79"
	Disc Diameter (Metric)	20.0mm
	Panel Thickness Max. (Imperial)	0.08"
	Panel Thickness Max. (Metric)	3.00mm

generated on: 1/26/2018

151-00367

HellermannTyton

Product Dimensions	Panel Thickness Min. (Imperial)	0.02"
	Panel Thickness Min. (Metric)	0.50mm
	Mounting Hole Diameter D (Metric)	6.2 - 6.7 mm
	Mounting Hole Diameter D Min. (Imperial)	0.244"
	Mounting Hole Diameter D Max. (Imperial)	0.26"
Material and Specifications		
	Material	Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS)
	Material Shortcut	PA66HIRHS
	Flammability	UL 94 HB
	Operating Temperature	-40°F to +221°F (-40°C to +105°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	900
	Package Quantity (Metric)	900Pieces
	Customs Number(Schedule B)	3926909987
	Weight (Metric)	0.5kg