

Representative Image

Catalog No. TY400-50X-100

Description: CBL TIE 14IN UV BLACK NYL 50LB

UPC No 5414363075363

Home > Wire & Cable Management > Ty-Rap > Cable ties

"Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius, Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, UL/IEC 62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 365mm, Width of 4.8mm, Thickness of 1.24mm , Tensile Strength Rating of 220 Newtons, 100 Pack"

Descriptors

Category	Cable ties
Special Features	The integrally formed polyamide pawl combines low insertion and high locking strength. The low profile head significantly reduces the potential for snagging during installation. Quick and easy pull through increases productivity, reduces operator fatigue. Tail with finger grip design that helps operator grasp and pull ties snugly. Sure grip tab keeps the tail from popping out while being treated, then holds it it securely for final tightening by hand or tool

Specifications

Material	Nylon/Polyamide 6.6 UV Resistant
Color	Black
Lock Mechanism	Plastic Pawl
Tensile Strength	550 newtons , 124 pounds

Classifications

Brand Name	Catamount
Standard	UL E49405

Dimensions

Width	7.6mm , 0.299 in
Length	610 mm , 24.016 in
Thickness	1.6 mm , 0.063 in
Bundle Diameter	6 to 181.5 mm , 0.236 to 71.456 in

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant
POPs	POPs 28 Compliant

Downloaded from Arrow.com.

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
UL	E49405	N/A	N/A	N/A	N/A

Downloaded from Arrow.com.