Datasheet for part number ECIV2021-010S1H2C1A0

Our Catalog Part Number: ECIV2021-010S1H2C1A0
Our Global Manufacturing Part Number: 132055-6010
Brand: Cannon Product Category: EV Product Line: EV Series: EV

Product Datasheet	
Series	EVC IEC 62196 Type 2 connector vehicle inlet
Product Image	Current Rating
20A	Cable Rating
Level 2	Powering System
Single phase (250VAC)	Cable Length
1 m	Compression Limiter/Metal Inserts in Flange Holes
With compression limiter	Dust Cap/ Spring Cap
With spring cap (Opening to the right)	Drain Spout
With Drain spout with tube, 1 m long	Locking Device
Motorized switch assembly including connector and 300 mm cable	Rubber Boot
With rubber boot	Mounting Hole Pattern
Standard pattern	Flange Gasket
No flange gasket supplied	Temperature Range
-30°C to +50°C	Durability
10,000 mating cycles min	Sealing Requirements
IP 44 min per IEC 61851-1 and tested in accordance with IEC 60525	Certifications Connector
CE, ETL, IEC 62196-1 and IEC 62196-2	Certifications Cable
DIN EN 50620	Product Drawing

Specifications and dimensions subject to change.

Downloaded from Arrow.com.