








P1		P2
1	WHITE	8
2	ORANGE	7
3	BLACK	6
4	RED	5
5	GREEN	4
6	YELLOW	3
7	BLUE	2
8	BROWN	1



Note:

- Material: Housing-polycarbonate, clear
- Terminal-0.36[.014] thick phosphor bronze.
- Thick gold in localized gold plate.
- Area, Gold Flash over the remainder.
- Over 2.54mm[.000100] thick nickel underplate.

Part Number	Drawing Number	Wire Length "L"	Jacket Color	Cut Length
AT-S-26-8/8/B-5	A	1,525±20(5ft)	Black	1,525-1,535mm
AT-S-26-8/8/B-7	B	2,135±30(7ft)	Black	2,135-2,145mm
AT-S-26-8/8/B-10	C	3,050±60(10ft)	Black	3,050-3,060mm
AT-S-26-8/8/B-12	D	3,660±60(12ft)	Black	3,660-3,670mm
AT-S-26-8/8/B-14	E	4,270±60(14ft)	Black	4,270-4,280mm
AT-S-26-8/8/B-25	F	7,625±100(25ft)	Black	7,625-7,635mm
AT-S-26-8/8/B-50	G	15,250±150(50ft)	Black	15,250-15,260mm

Unit: mm



Scale	Free						Date	Name
TOLERANCE						Drawn	08.07.13	Wilson
X.	±X					Approved	08.07.13	Groll
X.X	±X							
X.XX	±X							
DIM	TOL					ASSMANN WSW components 1840 W. Drake Drive, Suite 101 • Tempe, AZ 85283 Toll Free: 1-877-277-6266 • Email: info@assmann.us		
X.°	±X°							
X.X°	±X°							
Angle	TOL	Id.	Modification	Date	Name			



Title	Modular cable - Straight
	8P8C 50μ", 26AWG, Black, 5-50 feet
ASSMANN WSW-No.	AT-S-26-8/8/B-xx
Drawing-No.	
Replace	rev00
Sheet	1/1