

Han-Modular Compact side entry M25



Image is for illustration purposes only. Please refer to product description.

Part number	19 14 001 0501
Specification	Han-Modular Compact side entry M25
HARTING eCatalogue	https://harting.com/19140010501

Identification

Category	Hoods / Housings
Series of hoods/housings	Han-Modular [®] Compact
Type of hood/housing	Hood

Version

Size	Modular Compact
Version	Side entry
Number of cable entries	1
Cable entry	1x M25
Locking type	Single locking lever

Details	Rated voltage ≤630 V
	Rated impulse voltage ≤6 kV
Details	Pollution degree 3
	For a complete connector the specified voltage rating is the maximum level which can be achieved. In cases where the used module(s) do offer lower voltage ratings, then these lower ratings are valid. Higher voltage ratings in individual applications can be approved in coordination with HARTING.

Pack contents	4 screws are included within the delivery
---------------	---

Technical characteristics

Tightening torque	1 Nm Fixing screws M3
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Mating cycles	≥500



Pushing Performance
Since 1945

Technical characteristics

Degree of protection acc. to IEC 60529	IP65 locked condition
--	-----------------------

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

Specifications	IEC 61984
Approvals	CE

Commercial data

Packaging size	1
Net weight	89 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140124271
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466