

	1	2	3	4	5	6	7							
A				A= 1.00x No. of Spaces B= A + 5.6 C= A + 2.1 *Available in 4 through 39 circuits		NOTES: 1.Body : PA6T with 30% GF. UL94V-0 Color Nature(Ivory) 2.Slider : PA6T with 30% GF. UL94V-0 Color Black 3.Contact : Phosphor Bronze 4.Fixed tab :Brass with Tin plated 5.Plating: Matte Tin plated over Nickel 6.Contact style: Downside contact AFFC25-xx-100-SHB-x Packing: R= Tape & Reel T= Tube			A					
B									B					
C									C					
D									D					
E									E					
F									F					
G	RoHS compliant Unit: mm			Scale		Free	Date		Name	Customer-No.	G			
TOLERANCE				Drawn		08.07.2008	N.Schulz	ASSMANN WSW-No. AFFC25-xx-100-SHB-x	rev04	H				
.X				±0.15	④	Correction the pin counts 32 Pin Max	22.03.2016				Winnie	Approved	22.03.2016	Winnie
.XX				±0.10	③	Update	07.08.2014				Amy			
H	DIM		TOL	②	Redraw	03.08.2009	Dean	Drawing-No.		ASS 2687 CO	SHEET 1 / 2	H		
X.°		±1°	①	Drawn	08.07.2008	N.Schulz	Replace							
X.X°		±X°	Id.	Modification	Date	Name	ASSMANN WSW components							
Angle		TOL												
	1	2	3	4	5	6	7	SV1060						

