



Mean Well Switching Power Supply - 24VDC, 18.8A

 TOL-16265 ROHS 



DESCRIPTION

FEATURES

DOCUMENTS

- Output Voltage: 24VDC
- Output Current Range: 0--18.8A
- Output Rated Power: 451.2W
- Input Voltage Range: 90--132VAC / 180--264VAC by switch, 254--370VDC
- Forced air cooling by built-in DC ball bearing fan
- Built-in cooling Fan On/Off control
- Built-in constant current-limiting circuit
- Built-in remote sense function
- LED indicator for power on

Tags

MEAN WELL | POWER | POWER SUPPLY | SINGLE OUTPUT | TOOLS

 images are CC BY 2.0

   

COMMENTS 0

REVIEWS 0

Comments

Looking for answers to technical questions?

We welcome your comments and suggestions below. However, if you are looking for solutions to technical questions please see our [Technical Assistance](#) page.

[Log in](#) or [register](#) to post comments.



 START SOMETHING.



Email address

SUBSCRIBE TO NEWSLETTER

ABOUT SPARKFUN

[Read Our Story](#)

[Press & Media](#)

[SparkFun Education](#) 

[Job Openings](#)

PARTNER WITH US

[See Our Partners](#)

[Become a Distributor/Reseller](#)

[Receive Volume Discounts](#)

[Build a Custom Kit](#)

[Apply for a Hardware Donation](#)

SUPPORT

[Customer Support](#)

[Purchase Orders & Payment](#)

[Terms](#)

[Technical Assistance](#)

[FAQs](#)

[Contact Us](#)

SITE INFORMATION

[Terms of Service](#)

[Privacy Policy](#)

[Compliance](#)

[Site Map](#)

