





MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 91929

**SMALL PRECISION
LIMIT SWITCH**

CATALOG LISTING


914CE16-18



- NOTES
1 - ZINC HOUSING FINISHED WITH GRAY PAINT
2 - SWITCH WILL ACTUATE IN BOTH DIRECTIONS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS		ELECTRICAL DATA		SCALE FULL		DO NOT SCALE PRINT	
OPERATING FORCE — — — 3 IN. LB MAX		CONTACT ARRANGEMENT		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE			
RELEASE FORCE — — — 10 IN. OZ MAX		S P D T					
PRETRAVEL — — — — — 30° MAX		L109 5A 1/10HP 125 OR <u>250</u> VAC  		ONE PLACE (.01) ± .030			
DIFFERENTIAL TRAVEL — — — 3° MAX				TWO PLACE (.00) ± .015			
OVERTRAVEL — — — — — 40° MIN				THREE PLACE (.000) ± .005			
				ANGLES ±			
				WEIGHT			

M 914CE16-18

**DRAWING
NUMBER**

1

ISSUE

REPLACES

RELEASE NO. PR-17749

CHECK

CHECK

REVISIONS

DDM/CAD

DRAWN

CHECK

20 OCT 89

MAM