

Frame Han 24HPR EasyCon H. sh. st. i



Image is for illustration purposes only. Please refer to product description.

Part number	09 40 024 9951
Specification	Frame Han 24HPR EasyCon H. sh. st. i
HARTING eCatalogue	https://harting.com/09400249951

Identification

Category	Accessories
Series of hoods/housings	Han® HPR EasyCon
Type of accessory	Frame
Description of the accessory	for standard inserts for Han-Modular® hinged frames

Version

Gender	Male Female
Size	24 B
Field of application	Hoods/housings for harsh outdoor environments
Pack contents	2x M4/M5 distance bolts (AF 7) 2x M5/M6 distance bolts (AF 7) 2x M4 screw 2x washer SK S4

Technical characteristics

Tightening torque	1.5 Nm Fixing screws M4 6 Nm Distance bolt
Mating cycles	≥100

Material properties

Material (accessories)	Stainless steel
RoHS	compliant
ELV status	compliant

Page 1 / 2 | Creation date 2025-05-08 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application.

HARTING Electric Stiftung & Co. KG | Wilhelm-Hartung-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Commercial data

Packaging size	1
Net weight	80 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140194281
eCl@ss	27440210 Fixing element for industrial connectors
ETIM	EC002310
UNSPSC 24.0	39121466