






NOTES:

- Insulator: PBT
- Contacts: Phosphorbronze, t=0.25mm
- Shell: Brass t=0.3 / Finish: Nickel Plated
- Withstanding Voltage: 500V AC (1 min)
- Insulation Resistance: 1000M min.
- Rated Voltage and Current: 1.5A at 250V AC min.

Scale	1:1						Name	Item No.		
TOLERANCE						Drawn	10.19.11	Chappell	A-USB-A-3P-R (Version 1.1, 5μ” Gold)	
X.X	±0.40					Approved			A-USB/2-A-3P-R (Version 2.0, 30μ” Gold)	
X.XX	±0.25								Title USB, Type A, 3 Port	
X.XXX	±0.15									
Angle	±3°								Drawing No.	
									rev00	
										
			Modification	Date	Name				Replace	Sheet

