Part Number : 1301550141
Product Description : Watertite Extreme Connector with California Style Locking Blade, 3 Pole/4 Wire, Non-NEMA, 50A/125V/250V, Cord Grip Body Size F5
Series Number : 130155
Status : Active
Product Category : Wiring Devices
Engineering Part Number : CS63W64



Documents and Resources

Drawings

1301550141_sd.pdf

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Downloaded from Arrow.com.

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Wiring Devices
Series	130155
Description	Watertite Extreme Connector with California Style Locking Blade, 3 Pole/4 Wire, Non-NEMA, 50A/125V/250V, Cord Grip Body Size F5
IP Rating	IP67
NEMA Configuration	Non-NEMA Locking CA
Product Name	Watertite Extreme
Specialty	N/A
Type	Connector
UPC	78678801470

Agency

CSA	LR6837
UL	E10176

Electrical

Current - Maximum per Contact	50.0A
GFCI	No
Voltage - Maximum	250V

Physical

Cord Grip Body Size	F5 1 1/4"
Cord Type	N/A
Flange	No
Flip Lid	No
Gender	Female
Length	N/A
Lighted Connector	No

Downloaded from Arrow.com.

Locking Blade	Yes
Net Weight	773.827/g
Poles	3-pole/4-wire
Receptacle Type	Single

This document was generated on May 25, 2026

Downloaded from Arrow.com.