

SEK CAB FLAT COLOR TW AWG28/7 26P 30,48m



Image is for illustration purposes only. Please refer to product description.

Part number	09 18 026 7006
Specification	SEK CAB FLAT COLOR TW AWG28/7 26P 30,48m
HARTING eCatalogue	https://b2b.harting.com/09180267006

Identification

Category	System cabling
Element	Bulk cables
Specification	Not assembled
Type of cable	Copper cable (flat)
Description of the cable	Twisted pair

Version

Cable length	30.48 m
Number of cores	26
Core structure	AWG 28/7

Technical characteristics

Impedance	122 Ω
Limiting temperature	-20 ... +105 °C
Signal run time @ 20 °C	≤ 5.35 ns/m

Material properties

Material (cable)	PVC
Colour (cable)	Colour coded
Material flammability class acc. to UL 94	VW-1
RoHS	compliant
ELV status	compliant
China RoHS	e



Pushing Performance

Material properties

REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No
California proposition 65	Yes
California proposition 65 substances	Antimony trioxide

Specifications and approvals

UL / CSA	UL 758 AVL2.E42769
----------	--------------------

Commercial data

Packaging size	1
Net weight	66.4 g
Country of origin	USA
European customs tariff number	85444993
eCl@ss	27061801 Data and communication cable (copper)