



Part Number : [1300940519](#)
Product Description : Bus-Drop Support Grip,
Locking Bale, Cable Diameter 17.78-21.59mm
(.700-.850"), Approximate Break Strength 861.83kg
(1900 lbs)
Series Number : 130094
Status : Active
Product Category : Cable Grips
Engineering Number : 36589



Documents & Resources

Drawings

- [1300940519_sd.pdf](#)
- [PK-130227-004-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not saleable
China RoHS	Not saleable
EU ELV	Not saleable
Low-Halogen Status	Not saleable
REACH SVHC	Not saleable
EU RoHS	Not saleable

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Cable Grips
Series	130094
Description	Bus-Drop Support Grip, Locking Bale, Cable Diameter 17.78-21.59mm (.700-.850"), Approximate Break Strength 861.83kg (1900 lbs)
Product Name	Bus-Drop
Type	Support Grip
UPC	78678836589

Agency

CSA	LR32159
UL	E76954

Physical

Approximate Break Strength	861.83kg (1900 lbs)
Bale Length	0.406m (16.00")
Body Style	Straight
Cable Diameter	17.78-21.59mm (.700-.850")
Color - Grommet	N/A
Eye Type	Locking Bale
Gender	N/A
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	0.216m (8.50")
Net Weight	62.003/g
Number of Holes	N/A

O-Ring	N/A
Thread Size	N/A

This document was generated on Sep 22, 2025