



Part Number : [191640012](#)

Product Description : Perma-Seal Female Quick Disconnect for 22-18 AWG Wire, Tab Size 6.35 x 0.81mm, Carton

Series Number : 19164

Status : Active

Product Category : Quick Disconnects

Engineering Part Number : SAA-2140



Documents and Resources

Drawings


[191640012_sd.pdf](#)

Specifications

[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19164
Description	Perma-Seal Female Quick Disconnect for 22-18 AWG Wire, Tab Size 6.35 x 0.81mm, Carton
Product Name	Perma-Seal
Type	Standard Quick Disconnect
UPC	800753113008

Electrical

Voltage - Maximum	600V
-------------------	------

Physical

Barrel Type	Closed
Color - Resin	Red
Gender	Female
Glow-Wire Capable	No
Insulated	Partial
Insulation	NiAc
Lock to Mating Part	No
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.943/g
Orientation	Straight
Packaging Type	Carton

Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Tab Thickness	0.81mm
Tab Width	6.35mm
Temperature Range - Operating	-55° to +125°C
Wire Insulation Diameter	5.97mm max.
Wire Size (AWG)	18, 20, 22

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Insulkrimp Quick Disconnect Terminals, 22-10 AWG	<u>640010400</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640050400</u>

This document was generated on May 27, 2026