TE Connectivity: Every Connection Counts
© 2016 TE Connectivity Ltd. family of companies. All Rights Reserved

CONNECTORS

BOX MOUNT D-SUB CONNECTORS



✔ Active

TE CONNECTIVITY (TE)

HD90 44 POS GMT ASY PLUG

AMPLIMITE

211675-4
TE Internal Number: 211675-4

EU RoHS Compliant
EU ELV Compliant

Connector Style Plug

Number of Positions 44

Power/Signal/Coax Combination No

Shell Size 3

Contact Style Crimp Snap-In

PRODUCT DRAWING
English

3D PDF

DOCUMENTATION

Product Drawings

PLUG ASSY, AMPLIMITE, 44 POSN., SIZE 3, SERIES 90, NON-MAGNETIC, SPECIAL WITH GROMMET
PDF
English

CAD Files

3D PDF
PDF
3D

Customer View Model
3D_IGS.ZIP
English

Customer View Model

Downloaded from Arrow.com.

2D_DXF.ZIP
English

Customer View Model

3D_STP.ZIP
English

FEATURES

Please review product documents or contact us for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector Style Plug
Shell Size 3
Blindmate No
Product Type Connector

Configuration Features

Number of Positions 44
Power/Signal/Coax Combination No

Body Features

Non-Magnetic Yes
Shell Material Brass
Shell Plating Material Gold
Retention Clip Material Copper Alloy

Contact Features

Contact Style Crimp Snap-In
Contact Size 22

Mechanical Attachment

Mounting Hole Diameter 3.05 mm [.12 in]

Operation/Application

ULTRA-LITE Connector No

Industry Standards

NASA Qualification No

Packaging Features

Packaging Method Package

Other

Comment Grommet provided for cable strain relief.

Downloaded from Arrow.com.

Statement of Compliance

Statement of Compliance

PDF

Downloaded from Arrow.com.