



C2G
1.6ft (0.5m) Velocity™ TOSLINK® Optical Digital Cable (TAA Compliant)
 Part No. 40389



Optical digital cables use light to transfer the signal; thus completely eliminating any chance for RFI, EMI or ground loop interference. Connect the Velocity TOSLINK cable to your DVD player, CD player, satellite receiver, game console or other digital audio equipment for clear, fully detailed sound. Manufactured from high quality PMMA optical fiber with a polished lens and gold-plated collet, the Velocity cable provides an accurate digital signal. The low loss PMMA Poly (methyl methacrylate) core ensures low distortion. The non-slip rubber grip connector enables easy installation while the stylish PVC jacket adds flexibility and durability for years of listening pleasure. Protective plastic cover protects lens from dust, dirt, and other material.

Features & Benefits

Supports optical digital audio

Low loss PMMA Poly (methyl methacrylate) core ensures low distortion

Included end cap protects the conductor from dust, dirt and other material

Specifications

General Info

Product Line	C2G	Color	Blue
UPC Number	757120403890	Country Of Origin	China
Application Sector	Commercial, Residential	Warranty Type	Lifetime
Type	Cable		

Dimensions

Product Length US	1.6 FT	Cable Length	1.6 ft
-------------------	--------	--------------	--------

Trade Programs

TAA Compliant	Yes
---------------	-----

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Cable Type	Audio
Jacket Rating	Standard / Non-Rated	Connector 2	Toslink Male
Connector 1	Toslink Male		
