



**Part Number :** [393570009](#)  
**Product Description :** 3.50mm Pitch Beau Eurostyle  
Fixed Mount PCB Terminal Block, 9 Circuits  
**Series Number :** 39357  
**Status :** Active  
**Product Category :** Terminal Blocks and Barrier  
Strip  
**Engineering Part Number :** MX-MTB09008-0N



## Documents and Resources

### Drawings

[393570009 sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

## Product Environment Compliance

### Compliance

|                    |                                                                                                         |
|--------------------|---------------------------------------------------------------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                                                                            |
| China RoHS         |  per SJ/T 11365-2006 |
| EU ELV             | Not Relevant                                                                                            |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21                                                                          |
| REACH SVHC         | Contains Lead per D(2025)7771-DC (04 Feb 2026)                                                          |
| EU RoHS            | Compliant with Exemption 6(c) per EU 2015/863                                                           |

### [Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

## Part Details

### General

|                |                                                                        |
|----------------|------------------------------------------------------------------------|
| Status         | Active                                                                 |
| Category       | Terminal Blocks and Barrier Strip                                      |
| Series         | 39357                                                                  |
| Description    | 3.50mm Pitch Beau Eurostyle Fixed Mount PCB Terminal Block, 9 Circuits |
| Application    | Wire-to-Board                                                          |
| Component Type | One Piece                                                              |
| Product Name   | Eurostyle Fixed Mount                                                  |
| Type           | PCB Terminal Blocks and Connectors                                     |
| UPC            | 756054634196                                                           |

### Agency

|    |        |
|----|--------|
| UL | E48521 |
|----|--------|

### Electrical

|                               |       |
|-------------------------------|-------|
| Current - Maximum per Contact | 17.5A |
| Voltage - Maximum             | 300V  |

### Physical

|                    |       |
|--------------------|-------|
| Circuits (Loaded)  | 9     |
| Circuits (maximum) | 9     |
| Color - Resin      | Black |

|                               |                            |
|-------------------------------|----------------------------|
| Entry Angle                   | Horizontal                 |
| Flammability                  | 94V-0                      |
| Lock to Mating Part           | No                         |
| Net Weight                    | 11.000/g                   |
| Number of Rows                | 1                          |
| Orientation                   | Vertical                   |
| Panel Mount                   | No                         |
| PCB Retention                 | No                         |
| PCB Thickness - Recommended   | 1.60mm                     |
| PC Tail Length                | 3.50mm                     |
| Pitch - Mating Interface      | 3.50mm                     |
| Pitch - Termination Interface | 3.50mm                     |
| Polarized to Mating Part      | No                         |
| Shrouded                      | Shrouded                   |
| Stackable                     | Yes                        |
| Temperature Range - Operating | -30° to +85°C              |
| Wire Size (AWG)               | 16, 18, 20, 22, 24, 26, 28 |
| Wire Size mm <sup>2</sup>     | 0.20-1.00                  |

### Solder Process Data

|                              |      |
|------------------------------|------|
| Lead-Free Process Capability | WAVE |
| Max-Cycle                    | 5    |
| Max-Temp                     | 260  |

---

This document was generated on Apr 26, 2026