

Product Line

- DeepTronica >
- Single Pair Ethernet >
- ZConnect >
- Ceres >
- X-Lok >
- Accessory
- Middle Size
- Mini Size
- Large Size
- Standard Size
- M Series >
- FLOS & FLOS+ >
- Power >
- RBL >
- HS-Lok >
- NMEA 2000 >
- Heavy Duty Shielded >
- RJ >
- USB >
- SSL >
- HDMI >
- DVI >
- Fiber Optic >
- RF >
- Cable Joiner >
- Cable Gland >
- Pressure Relief Vent >
- LED Light Guide >
- D-Sub >



BB-02AFMM-QL8D01

Operating Temperature: -20°C ~ +80°C
Transmission Speed: N/A
Shielded: Plastic, Non-shielded
Jacket Material: PVC
Certificate: UL2238, UL50e

You must login first for view the price

Quantity - 1 +

Add to Cart Inquiry

Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type Search

X-Lok, Standard...
AB-BB02FL-BBHL...
-20°C ~ +80°C

- 0 +

☐

X-Lok, Standard...
AB-BB02FL-BBHL...
-20°C ~ +80°C

- 0 +

☐

X-Lok, Standard...
AB-BB02FL-BBHL...
-20°C ~ +80°C

- 0 +

☐

X-Lok, Standard...
AB-BB02FL-BBHL...
-20°C ~ +80°C

- 0 +

☐

X-Lok, Standard...
AB-BB02FL-BBHL...
-20°C ~ +80°C

- 0 +

☐

X-Lok, Standard...
AB-BB02FL-BBHL...
-20°C ~ +80°C

- 0 +

☐

Add to Cart Inquiry

Specifications	Download / CAD
Nominal Current 10A	Connector Type Overmolded
Shielded Plastic, Non-shielded	No. of Contacts 02
Connector Gender Female	Backshell Straight
Mating Style Push Lock	IP Rating IP68
Assembly Style N/A	
More Options	

People Also Bought

- 
BB-02AFMM-QL8D01
- 
M12A10ML-12AFL-...
- 
CB-04PMFM-SL7A01
- 
BB-02BFMM-SR6A04
- 
DC-05BFFA-SL7001