

Part Number : 1062835003

Series Number : 106283

Product Category : Fiber Optic Cable Assemblies

Product Description : Quad Small Form-factor Pluggable Plus (QSFP+) Optical Breakout Cable Assembly, 4 TX, 4 RX; 8 Fiber MTP - 8 LC Multimode 50/125 μ m 3.00mm Round Cable Plenum, Standard Bandwidth(OM2), 5.0m (16.40') Length

Status : Active

Documents & Resources

Drawings

Drawing 1062835003_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2020)9139-DC (19 Jan 2021)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Fiber Optic Cable Assemblies
Series	106283
Description	Quad Small Form-factor Pluggable Plus (QSFP+) Optical Breakout Cable Assembly, 4 TX, 4 RX; 8 Fiber MTP - 8 LC Multimode 50/125µm 3.00mm Round Cable Plenum, Standard Bandwidth(OM2), 5.0m (16.40') Length
Connector to Connector	MTP-to-LC
Mode	Multimode Enhanced
Product Family	zQSFP+ and QSFP+ Integrated Product Solutions
Product Name	MPO, QSFP Plus, QSFP+
UPC	822350976763

Physical

Boot Type	N/A
Cable Length	5.0m
Cable Size	3.00mm
Fiber (Core/Cladding)	50/125µm
Net Weight	82.234/g
Single Ended	No
Wire/Cable Type	Round

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

This document was generated on May 06, 2024