


MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING
YZ-2RW84510-A2
AYK9501

CATALOG LISTING
YZ-2RW84510-A2
PAGE 1 OF 1
REPLACES X113536-YZ
RELEASE NO. 202680
CHECK
REVISIONS
A 0000874
JLH
14 JUL 93
B 0017586
TSG
09 JAN 06
R J
CHECK
27 MAR 01
S A V
CHECK
27 MAR 01
DRAWN
C S L
27 MAR 01
MASTER



2X 6-32 UNC X (.219)
BINDING HEAD COMBINATION
TERMINAL SCREW AND
CUPWASHER

NOTE
 $\triangle$ MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF $\phi .139$ MAX ON $1.000 \pm .002$ CENTERS

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL	DO NOT SCALE PRINT
OPERATING FORCE — — — — — 1 OZ MAX	CONTACT ARRANGEMENT S P N O	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
RELEASE FORCE — — — — — 1/8 OZ MIN	L96 15A 125, 250 OR 480 VAC 1/8HP 125 VAC, 1/4HP 250 VAC 1/2A 125 VDC, 1/4A 250 VDC	ONE PLACE (.0) $\pm .030$	
DIFFERENTIAL TRAVEL — — — .007 - .050		TWO PLACE (.00) $\pm .015$	
OVERTRAVEL — — — — — .219 MIN		THREE PLACE (.000) $\pm .005$	
BREAK DISTANCE — — — — — .020 MIN	L288 L306 L315	ANGLES $\pm$	
	CE 05	WEIGHT .073 LB	

16A 250V $\sim$ T85 5E4