

Quick Links

Cross reference

RoHS/LF P/N Search

Industry Standards

Alphabetical List

Documentation

3D model search

Customer drawing search

Multi Selection Search

Search by category

Start > Search=V503315200J0G* > V503315200J0G

V503315200J0G

V503315200J0G - Terminal Blocks : Pluggable plug, 3.81mm pitch, Din-rail mounting, A type, horizontal wire-inlet, 3 position



ACTIVE

Distributor Stock

Print Datasheet

FCI Brings You More

Contact our sales/technical support

Sample request

Customer drawing

Environmental Compliance Report

Specifications

Download document

Mating Half

Dimensional	
Strip length (Wire)	6 mm
Solid wire size (AWG)	14 to 28
Stranded wire size (AWG)	14 to 28
Pitch	3.81 mm
Screw Size	M2
General	
Gender	Male plug
Packaging	Box
Product Type	Screw Pluggable System
Series	V5
Number of Positions	3
Electrical	
Withstanding Voltage	1.6 kV
Current rating	8 A
Voltage rating	300 V
Mechanical	
Number of mating cycles	200
Physical	
Color (Housing)	Green
Conductor entry angle	0°
Material (Housing)	Thermoplastic UL94V-0
Terminal material	Brass
Terminal plating	Tin
Screw material	Steel
Screw plating	Zinc
Clamp material	Brass
Clamp plating	Nickel
Connection Type	Screw connection
Temperature (Operating - range)	-40 to 115 Celcius
Torque	2.17 Lb-in
Approvals / Certifications	
Approvals / Certifications	cULus

Disclaimer : The information above is for reference only. For more technical details, refer to product specification and application specification.

Downloaded from Arrow.com.